

# EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

## Energiebedrijven

Subrack with reinforced horizontal rails and side panels for backplane mounting.



## CERTIFICERINGEN



## KENMERKEN

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, - 102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

## SPECIFICATIES

Table 1/3

| Catalogusnummer | Rack Height | Diepte | Package Quantity | For Mounting | Board Depth | EMC Gasket Type |
|-----------------|-------------|--------|------------------|--------------|-------------|-----------------|
| 24567-149       | 3 U         | 295 mm | 1                | Backplane    | 160 mm      | Textile         |
| 24567-449       | 6 U         | 295 mm | 1                | Backplane    | 160 mm      | Textile         |

Table 2/3

| Catalogusnummer | Shock and Vibration Tolerance | Handle Included | Montage | Voldoet aan                                                                               | EMC Shielding | Product Type    |
|-----------------|-------------------------------|-----------------|---------|-------------------------------------------------------------------------------------------|---------------|-----------------|
| 24567-149       | 25 g (force)                  | Ja              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3 | Ja            | Subrack/Chassis |
| 24567-449       | 25 g (force)                  | Ja              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3 | Ja            | Subrack/Chassis |

Table 3/3

| Catalogusnummer | Rack Width | Statische belasting |
|-----------------|------------|---------------------|
| 24567-149       | 84 HP      | 25 kgf              |
| 24567-449       | 84 HP      | 25 kgf              |

## ADDITIONAL PRODUCT DETAILS

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WAARSCHUWING

---

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**