

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Energiebedrijven

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICERINGEN



KENMERKEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Roestvrij staal
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Roestvrij staal
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Roestvrij staal
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Roestvrij staal
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Roestvrij staal
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Roestvrij staal
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Roestvrij staal

Table 2/3

Catalogusnummer	Handle Included	Montage	Voldoet aan	EMC Shielding	Product Type	Rack Width
24563-191	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-192	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-193	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-194	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-491	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-492	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP
24563-493	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP

Catalogusnummer	HandleIncluded	Montage	Voldoet aan	EMC Shielding	Product Type	Rack Width
24563-494	Nee	Rack	IEC 60297-3-103	Nee	Subrack/Chassis	84 HP

Table 3/3

Catalogusnummer	Statische belasting
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE