


EuropacPRO 19" Subrack Kit for Railway, Shielded, SNCF

Energiebedrijven

Subrack for Railway applications, conform to SNCF Standard.



CERTIFICERINGEN



KENMERKEN

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Rack Width	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
21500-028	6 U	84 HP	1	Backplane	220 mm	Textile
21500-030	3 U	84 HP	1	Backplane	220 mm	Textile
21500-068	3 U	36 HP	1	Backplane	220 mm	Textile
21500-071	6 U	36 HP	1	Backplane	220 mm	Textile

Table 2/3

Catalogusnummer	Shock and Vibration Tolerance	Handle Included	Montage	Voldoet aan	Diepte	EMC Shielding
21500-028	5 g (force)	Ja	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Ja
21500-030	5 g (force)	Ja	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Ja
21500-068	5 g (force)	Ja	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Ja
21500-071	5 g (force)	Ja	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Ja

Table 3/3

Catalogusnummer	Product Type	Statische belasting	Certificeringen
21500-028	Subrack/Chassis	15 kgf	RoHS, SNCF
21500-030	Subrack/Chassis	15 kgf	RoHS, SNCF
21500-068	Subrack/Chassis	15 kgf	RoHS

Catalogusnummer	Product Type	Statische belasting	Certificeringen
21500-071	Subrack/Chassis	15 kgf	RoHS

ADDITIONAL PRODUCT DETAILS

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE