

ISONV Insulated Conductor

Power Utilities



ISONV insulated down conductor is a specialized lightning protection down conductor that during operation may be subjected to impulse currents of up to 200 kA. ISONV is designed and tested to control separation distance and arcing. A semiconductive outer layer is used to minimize voltage gradients under lightning conditions.

KENMERKEN

Provides protection of equipment against lightning strike flashover by providing an insulated path to ground via an equivalent separation distance

Field terminated with separately ordered termination kits

SPECIFICATIES

Impulsstroom (Iimp): 200 kA 10/350 µs

Table 1/1

Catalogusnummer	Equivalente scheidingsafstand	Installatietemperatuur	Bedrijfstemperatuur
ISONV50	50 cm	-20 to 50 °C	-40 to 90 °C
ISONV70	70 cm	-20 to 50 °C	-40 to 90 °C

AANVULLENDE PRODUCTGEGEVENS

Available in 1 m increments up to 1,000 m.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE