

Novastar 19" Panel/Slide Mount

Energiebedrijven



Novastar 19" Panel/Slide Mount Kit with load capacity of 400 kg, ensures easy fitting of 19" components to depth members.

CERTIFICERINGEN



KENMERKEN

For recessed installation of 19" components

For fitting to depth members (25 mm grid)

Load carrying capacity 400 kg

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Package Quantity	Kleur	Color Code	Hoogte	Product Type
-----------------	-------------	------------------	-------	------------	--------	--------------

27230-172	6 U	1	Black Grey	RAL 7021	267.1 mm	Slide Mount
27230-173	9 U	1	Black Grey	RAL 7021	400.45 mm	Slide Mount
27230-174	12 U	1	Black Grey	RAL 7021	533.8 mm	Slide Mount
27230-175	16 U	1	Black Grey	RAL 7021	711.6 mm	Slide Mount
27230-176	20 U	1	Black Grey	RAL 7021	889.4 mm	Slide Mount
27230-177	25 U	1	Black Grey	RAL 7021	1111.65 mm	Slide Mount
27230-178	34 U	1	Black Grey	RAL 7021	1511.7 mm	Slide Mount
27230-179	38 U	1	Black Grey	RAL 7021	1689.5 mm	Slide Mount
27230-180	43 U	1	Black Grey	RAL 7021	1911.75 mm	Slide Mount
27230-181	47 U	1	Black Grey	RAL 7021	2089.55 mm	Slide Mount

Table 2/2

Catalogusnummer	Verpakkingseenheid
27230-172	Paar
27230-173	Paar
27230-174	Paar
27230-175	Paar
27230-176	Paar
27230-177	Paar
27230-178	Paar
27230-179	Paar

Catalogusnummer	Verpakkingseenheid
27230-180	Paar
27230-181	Paar

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE