

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding

Energiebedrijven



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets for assembly into a 19" rack.

CERTIFICERINGEN



KENMERKEN

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Retrofittable EMC shielding

Version with 19" mounting brackets

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

No visible screws; cladding parts removable without tools

Conforms with DIN EN 62368-1

SPECIFICATIES

Table 1/3

Catalogusnummer	Rack Height	Diepte	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-438	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-441	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-442	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-443	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-444	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-486	4 U	255.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-489	4 U	315.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-490	4 U	375.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-491	4 U	435.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-492	4 U	495.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-534	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-537	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-538	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-539	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Catalogusnummer	Rack Height	Diepte	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-540	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-201	5 U	255.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-204	5 U	315.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-205	5 U	375.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-206	5 U	435.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-207	5 U	495.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-345	5 U	255.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-348	5 U	315.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-349	5 U	375.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-350	5 U	435.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-351	5 U	495.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-570	2 U	255.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-573	2 U	315.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-574	2 U	375.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Catalogusnummer	Rack Height	Diepte	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-575	2 U	435.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-576	2 U	495.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Table 2/3

Catalogusnummer	Cooling Option	Voldoet aan	EMC Shielding	Hoogte	Product Family	Product Type
24571-438	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24571-441	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24571-442	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24571-443	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24571-444	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24571-486	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case

Catalogusnummer	Cooling Option	Voltoet aan	EMC Shielding	Hoogte	Product Family	Product Type
24571-489	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24571-490	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24571-491	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24571-492	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24571-534	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24571-537	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24571-538	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case

Catalogusnummer	Cooling Option	Voltoet aan	EMC Shielding	Hoogte	Product Family	Product Type
24571-539	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24571-540	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-201	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-204	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-205	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-206	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-207	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case

Catalogusnummer	Cooling Option	Voltoet aan	EMC Shielding	Hoogte	Product Family	Product Type
24572-345	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-348	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-349	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-350	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-351	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Case
24572-570	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-573	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case

Catalogusnummer	Cooling Option	Voldoet aan	EMC Shielding	Hoogte	Product Family	Product Type
24572-574	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-575	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-576	Nee	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case

Table 3/3

Catalogusnummer	Protection Rating	Rack Width	Statische belasting	Type	Breedte
24571-438	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-441	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-442	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-443	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-444	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-486	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-489	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Catalogusnummer	Protection Rating	Rack Width	Statische belasting	Type	Breedte
24571-490	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-491	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-492	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-534	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-537	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-538	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-539	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-540	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-201	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-204	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-205	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-206	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-207	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-345	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Catalogusnummer	Protection Rating	Rack Width	Statische belasting	Type	Breedte
24572-348	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-349	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-350	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-351	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-570	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-573	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-574	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-575	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-576	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE