

Enkelpolig verdeelblok

Energiebedrijven



CERTIFICERINGEN



KENMERKEN

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modulaire blokken met klikbevestiging voor het bouwen van meerpolige voedingsblokken

Easily clips onto DIN rail or mounts to panel with screws

95% fill ratio

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogeenvrij

SPECIFICATIES

Table 1/2

Catalogusnummer	Artikelnummer	Max Current Rating, IEC	Max Current Rating, UL/CSA	Line Side Connection	Load Side Connection	Line Side Max Conductor Size, IEC
UD2C12C630AL	569205	630 A	670 A	2 Cables	12 Cables	185 mm ²
UD-400A	569050	400 A	335 A	Kabel	11 Cables	185 mm ²
UDF12C800AL	569208	800 A	670 A	Flat Conductor	12 Cables	240 mm ²

Table 2/2

Catalogusnummer	Artikelnummer	Load Side Max Conductor Size, IEC	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certificeringen
UD2C12C630AL	569205	25 mm ²	1,000 VAC, 1,500 VDC	1,000 VAC/DC	UL
UD-400A	569050	35 mm ²	1,000 VAC/DC	600 V	cUR, CSA, UR, RoHS, CE, ERIFLEX UD
UDF12C800AL	569208	25 mm ²	1,000 VAC, 1,500 VDC	1,000 VAC/DC	UL

ADDITIONAL PRODUCT DETAILS

Increase the number of outputs with one input using a jumper on blocks with a Max Current Rating, IEC up to 160 A.

Blocks with 1,000 VAC/DC Max Working Voltage, UL are ideal for solar applications.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals

Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C

Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0,94	0,88	0,82	0,75	0,67	0,58	0,47

*environment around the terminal blocks inside the enclosure

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE