

Varistar CP Double Steel Door, Plain, 3-Point Locking

Energiebedrijven

Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

KENMERKEN

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Breedte	Kleur	Color Code	Voldoet aan
21630-086	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-087	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-088	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-089	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-090	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-091	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-440	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Catalogusnummer	Rack Height	Hoogte	Breedte	Kleur	Color Code	Voltoet aan
21630-441	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-442	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-443	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-444	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-445	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-446	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-447	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Catalogusnummer	Locking Type	Product Type	Protection Rating	Type	Works With
21630-086	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-087	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-088	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-089	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-090	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-091	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-440	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-441	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-442	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-443	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

Catalogusnummer	Locking Type	Product Type	Protection Rating	Type	Works With
21630-444	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-445	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-446	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-447	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE