

ETL Self-Regulating Heating Cable



nVent RAYCHEM ETL self-regulating trace heating cables provide energy efficient pipe freeze protection. R-ETL-A/B are suitable for on- or in-pipe applications, R-ETL(-A/B)-CR for on-pipe only. Each are available in two power outputs (10 and 16 W/m at 5 °C), supported by a full range of heat shrinkable connections and accessories.

KENMERKEN

Simple to design, with fluoropolymer jacket option for use in pipes

Easy to install: small geometry, cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIES

Nominal Thickness:	5,8 mm
Nominal Width:	8,5 mm
Min Bending Radius:	10 mm
Max Continuous Exposure Temperature, Power Off:	65 °C
Supply Voltage:	220 – 240 V
Minimale installatietemperatuur:	-20 °C
Kleur:	Zwart
Ground Path Type:	Braid
Geleidermateriaal:	Nickel-Plated Copper

Table 1/1

Catalogusnummer	Naam van het item	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Max Circuit Length, In-Pipe
924269-000	R-ETL-A	16 W/m	10 W/m	100 m	60 m
P000002042	R-ETL-B	25 W/m	16 W/m	100 m	60 m

Catalogusnummer	Naam van het item	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Max Circuit Length, In-Pipe
P000002043	R-ETL-A-CR		10 W/m	100 m	
P000002044	R-ETL-B-CR		16 W/m	100 m	

ADDITIONAL PRODUCT DETAILS

Maximum circuit lengths are based on 230 VAC supply and C-Type characteristic circuit protection devices, switch-on at 5 °C.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT