

GREEN LEAF Programmable Thermostat



nVent RAYCHEM GREEN LEAF is a modern design 'wall flush mounted' programmable thermostat for electrical floor heating. It can work in floor or room sensing mode or in room sensing mode with floor temperature limiter. Eco Design compliant thanks to the following functions: Room temperature control, with open window detection. For more details, please consult the Commissioning sheet (INST324 or EU2550). RAYCHEM GREEN LEAF is a modern design 'wall flush mounted' programmable thermostat for electrical floor heating. It can work in floor or room sensing mode or in room sensing mode with floor temperature limiter. Eco Design compliant thanks to the following functions: Room temperature control, with open window detection. For more details, please consult the Commissioning sheet (INST324 or EU2550).

KENMERKEN

Easy to set up and operate: smart 'leaf button'; simple timer event programming with possibility to group days

Flexible control: editable pre-set program; 7 day with 4 timer events; different temperatures possible for each timer event; timer or constant temperature function

Optimum heat management, with 2 sensors: ambient and floor sensor

Reliable during long life: 12 to 20 year total care warranty available, maintenance free

SPECIFICATIES

Table 1/4

Catalogusnummer	Naam van het item	Power Supply	Adjustable Differential	Regulation Type	Max Contact Load	Max Contact Voltage
1244-017312	R-GREEN-LEAF-EU	230 V	Nee	On/Off	13 A	230 V

Table 2/4

Catalogusnummer	Naam van het item	Current Rating	Sensor/Feeler Type	Remote Operation	Power Consumption, Standby	IP-classificatie
1244-017312	R-GREEN-LEAF-EU	13 A	Resistance Sensor	Nee	3 W	IP21

Table 3/4

Catalogusnummer	Naam van het item	RAL Number	IFTTT Support Available	Clock Type	Clock Model	Self Learning
1244-017312	R-GREEN-LEAF-EU	9005	Nee	Day Clock	Digitaal	Ja

Table 4/4

Catalogusnummer	Naam van het item	Hoogte	Breedte	Diepte
1244-017312	R-GREEN-LEAF-EU	86.3 mm	86.3 mm	41 mm

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT