

HTV Self-Regulating Heating Cable



nVent RAYCHEM HTV self-regulating heating cable is designed for freeze protection or process temperature maintenance of pipes and vessels up to 205°C continuously, with a maximum exposure temperature of 260°C. The HTV cable has a solid construction with a high power retention (HPR) heating core and pressure extruded electrical insulation. It is then integrated with a robust metallic braid and a chemically resistant fluoropolymer outer jacket.

KENMERKEN

High power retention (HPR) heating core

Power retention: At least 95% after 10 years

Design life: 30 years or more depending on application

Simplified design in hazardous area: T3 en T2

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIES

Supply Voltage:	190 – 277 V
Max Maintain or Continuous Exposure Temperature, Power On:	205 °C
Max Intermittent Exposure Temperature, Power On/Off:	260 °C
Max Cumulative Hours for Intermittent Exposure:	2000 h
Ground Path Type:	Braid
Area Classification:	Non-Hazardous; Hazardous
Outer Jacket Material:	High Temperature Fluoropolymer

Table 1/1

Catalogusnummer	Naam van het item	Nominal Power Output @ 10°C, 230V
P000004319	3HTV2-CT	9 W/m

Catalogusnummer	Naam van het item	Nominal Power Output @ 10°C, 230V
P000004320	5HTV2-CT	16 W/m
P000004321	8HTV2-CT	25 W/m
P000004322	10HTV2-CT	32 W/m
P000004323	12HTV2-CT	38 W/m
P000004324	15HTV2-CT	48 W/m
P000004325	20HTV2-CT	64 W/m
2000003152	28HTV2-CT	90 W/m

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT