

IceStop Self-Regulating Cable Kit



nVent RAYCHEM IceStop self-regulating trace heating cable kits provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

KENMERKEN

Simple to design

Easy to install, pre-terminated kits: 5 - 30 m, each with 8 m power cable, GM-RAKE fixing bracket and RayClic end seal

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIES

Nominal Height:	6 mm
Cold Lead Length:	8 m
Nominal Width:	14 mm
Nominal Power Output, In Air @ 0°C, 230V:	18 W/m
Nominal Power Output, In Ice Water @ 0°C, 230V:	36 W/m
Max Continuous Exposure Temperature, Power On:	65 °C
Max Intermittent Exposure Temperature, Power On:	85 °C
Nominal Cable Weight:	120 g/m
Supply Voltage:	220 – 240 V
Max Cumulative Hours for Intermittent Exposure:	800 h
Minimale installatietemperatuur:	-18 °C
Kleur:	Zwart
Ground Path Type:	Braid
Outer Jacket Material:	Modified Polyolefin
Heating Cable Technology:	Self-Regulating

Table 1/1

Catalogusnummer	Naam van het item	Lengte
-----------------	-------------------	--------

106160-000	GM-2X-SA-8	8 m
159067-000	GM-2X-SA-12	12 m
191808-000	GM-2X-SA-5	5 m
650854-000	GM-2X-SA-16	16 m
838627-000	GM-2X-SA-25	25 m
925956-000	GM-2X-SA-30	30 m
973923-000	GM-2X-SA-20	20 m

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT