

T2Green-5 Underfloor Heating Loose Cable



nVent RAYCHEM T2Green-5 is a constant power output floor heating cable delivering 5 W/m. Ideal for low energy buildings and passive houses, to provide additional comfort. It is dual conductor with a pre-terminated 2.5 m cold lead, available in lengths from 15 m to 115 m.

KENMERKEN

Simple and fast to install

Easy design: one cold lead connection due to dual wire cable design, different power outputs/m² obtained by varying the spacing

Low energy consumption and eco-design compatible: low power output heating cable, lower energy consumption when used with a nVent RAYCHEM smart thermostat

Reliable during long life: 12 year product warranty available

SPECIFICATIES

Cold Lead Length:	2,5 m
Nominal Power Output:	5 W/m
Buitenste diameter:	5,5 mm
Power Output, Typical:	30 – 50 W/m ²
Min Cable Spacing:	50 mm
Max Continuous Exposure Temperature, Power Off:	90 °C
Nominale spanning:	230 V
Ground Path Type:	Braid
Heating Cable Technology:	Constant Wattage
Kleur:	Groen
Outer Jacket Material:	Low Smoke Zero Halogen

Table 1/1

Catalogusnummer	Naam van het item	Voeding	Resistance Range	Lengte
SZ18300122	R-GR-15M/T0/SD	65 W	755.3 – 874.5 Ω	15 m

Catalogusnummer	Naam van het item	Voeding	Resistance Range	Lengte
SZ18300123	R-GR-20M/T0/SD	110 W	448.4 – 519.2 Ω	20 m
SZ18300124	R-GR-25M/T0/SD	160 W	315.9 – 365.8 Ω	25 m
SZ18300125	R-GR-35M/T0/SD	180 W	282.6 – 327.3 Ω	35 m
SZ18300126	R-GR-40M/T0/SD	230 W	220.4 – 255.2 Ω	40 m
SZ18300127	R-GR-50M/T0/SD	245 W	204.3 – 236.5 Ω	50 m
SZ18300128	R-GR-60M/T0/SD	340 W	148.2 – 171.6 Ω	60 m
SZ18300129	R-GR-70M/T0/SD	360 W	139.7 – 161.7 Ω	70 m
SZ18300130	R-GR-85M/T0/SD	425 W	117.9 – 136.5 Ω	85 m
SZ18300131	R-GR-100M/T0/SD	490 W	102.6 – 118.8 Ω	100 m
SZ18300132	R-GR-115M/T0/SD	560 W	89.6 – 103.7 Ω	115 m

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT