

CompacPRO Rear Panel With Vented Slots



The rear panel with vented slots can be used for the CompacPRO case. The rear panel is bolted on the rear frame.

CERTIFICERINGEN



KENMERKEN

Al material 3.0 mm

SPECIFICATIES

Materiaal:	Aluminium
Afwerking:	Geanodiseerd
Werkt met:	Omkastingen
Productserie:	CompacPRO
Type:	Achterpaneel
Producttype:	Zijpaneel

Table 1/1

Catalogusnummer	Rekhoogte	Rekbreedte	Hoeveelheid in verpakking	Snelle verzending
30823-027	3U	63HP	1	Nee
30823-033	4U	42HP	1	Nee

Catalogusnummer	Rekhoogte	Rekbreedte	Hoeveelheid in verpakking	Snelle verzending
30823-036	4U	63HP	1	Nee
30823-021	3U	28HP	1	Nee
30823-024	3U	42HP	1	Nee
30823-518	4U	84HP	1	Nee
30823-512	2U	84HP	1	Nee
30823-045	6U	63HP	1	Nee
30823-015	2U	42HP	1	Nee
30823-521	6U	84HP	1	Nee
30823-515	3U	84HP	1	Nee

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE