

240 Card-Lok

CATALOGUSNUMMER

240-4.80H



The Series 240 features a higher weight, narrow profile ideal for densely populated enclosures.

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CERTIFICERINGEN



KENMERKEN

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

For cold wall applications

Profile 6.10 mm (0.240") x 4.57 mm (0.180")

3 segment, non-shafted design

Weight 0.86 g/cm (0.077 oz/')

Flexible mounting options

Min expansion 5.59 mm (0.220")

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

DSCC 84103 / DSCC CID 59590

Screw actuated

Average clamp force (4.80", black anodized) = 314 lbs

PRODUCTKENMERKEN

Producttype: PCB-houder

Materiaal: Aluminium

Type: Zonder as

Thermische prestaties: Gemiddeld

Profiel: 6.10 x 4.57 mm

Klemkracht: 136 – 181kgf

Breedte opening: PCB + (5.0 - 5.9 mm)

AANVULLENDE PRODUCTGEGEVENS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE