

Guide Rail Accessories for Heavy PCBs, Extra Strong



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICERINGEN



KENMERKEN

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

SPECIFICATIES

Materiaal:	Aluminium
Afwerking:	Geanodiseerd
Werkt met:	Subracks; Omkastingen; Chassis
Productserie:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Producttype:	Geleiderail
Type:	Voor zwaar gebruik

Table 1/1

Catalogusnummer	Hoeveelheid in verpakking	Diepte plaat	Groefbreedte	Kleur	Snelle verzending
-----------------	---------------------------	--------------	--------------	-------	-------------------

34562-881	1	160mm	2	Zilver	Nee
34562-882	1	220mm	2	Zilver	Nee
34562-883	1	280mm	2	Zilver	Nee
34562-884	1	340mm	2	Zilver	Nee
34562-885	1	400mm	2	Zilver	Nee
34564-881	1	160mm	2.5	Zilver	Nee
34564-882	1	220mm	2.5	Zilver	Nee
34564-883	1	280mm	2.5	Zilver	Nee
34564-884	1	340mm	2.5	Zilver	Nee
34564-885	1	400mm	2.5	Zilver	Nee

AANVULLENDE PRODUCTGEGEVENS

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE