

Varistar CP Seismic Base Plate, Multi-Piece



Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

KENMERKEN

To cover the base opening

The multi-piece base plate is open at the rear (opening to rear 200 mm deep, no rear opening with 300 mm cabinet depth)

SPECIFICATIES

Producttype: Behuizing/reksokkel

Materiaal: Staal

Table 1/2

Catalogusnummer	Breedte	Diepte	Hoeveelheid in verpakking	Kleur	Kleurcode	Voldoet aan
20630-293	600mm	600mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-294	600mm	800mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-295	600mm	1000mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-296	600mm	1200mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-297	800mm	600mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-298	800mm	800mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2

Catalogusnummer	Breedte	Diepte	Hoeveelheid in verpakking	Kleur	Kleurcode	Voldoet aan
20630-299	800mm	1000mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2
20630-300	800mm	1200mm	1	Zwartgrijs	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Catalogusnummer	Afwerking	Type	Werkt met	Snelle verzending
20630-293	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-294	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-295	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-296	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-297	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-298	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-299	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee
20630-300	Gepoedercoat	Basisplaat, normaal	Varistar CP	Nee

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE