

VITA Conduction Cooled Assemblies



Order and manage one part number for entire CCA assembly including part marking and component labeling as well as card-locks, extractors, coding keys, EMC gaskets, and thermal pads.

CERTIFICERINGEN



KENMERKEN

Full design services including thermal analysis

Fast turnaround 3D printed CCA's and frames for fit checks

Downloadable standards compliant CAD templates - 3 U and 6 U templates available

Available in black anodize, chemical film, electroless nickel finishes

ESD Packaging Available

SPECIFICATIES

Table 1/2

Catalogusnummer	Werkt met	Klemkracht	Breedte opening	Ontwerpkenmerk	Thermische prestaties	Profiel
3U260VITA30.1 PS-700	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)		Beter	6.35 x 6.26 mm
3U260VITA46.0 PS-700	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)		Beter	6.35 x 6.26 mm

Catalogusnummer	Werkt met	Klemkracht	Breedte opening	Ontwerpkenmerk	Thermische prestaties	Profiel
3U260VITA48.2 PS-311	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)	Tolerantiecompensatie	Beter	6.35 x 6.26 mm
3U260VITA48.2 SS-311	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)	Tolerantiecompensatie	Beter	6.35 x 6.26 mm
3UVPX48.2-PS260HTSI-311	Conductiegekoelde behuizingen	272 – 318kgf	PCB + (7.0 - 7.9 mm)	Tolerantiecompensatie	Beste	6.35 x 6.26 mm
6U260IEEE1101.2PS-700	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)		Beter	6.35 x 6.26 mm
6U260VITA30.1 PS-700	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)		Beter	6.35 x 6.26 mm
6U260VITA46.0 PS-700	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)		Beter	6.35 x 6.26 mm
6U260VITA48.2 PS-311	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)	Tolerantiecompensatie	Beter	6.35 x 6.26 mm
6U260VITA48.2 SS-311	Conductiegekoelde behuizingen	136 – 181kgf	PCB + (7.0 - 7.9 mm)	Tolerantiecompensatie	Beter	6.35 x 6.26 mm

Table 2/2

Catalogusnummer	Rekhoogte	Voldoet aan	Oriëntatie	Afwerking	Materiaal	Snelle verzending
3U260VITA30.1 PS-700	3U	ANSI/VITA 30.1-2008	Primair		Aluminium	Nee
3U260VITA46.0 PS-700	3U	ANSI/VITA 46.0-2019	Primair		Aluminium	Nee
3U260VITA48.2 PS-311	3U	ANSI/VITA 48.2-2020	Primair	Black Anodized	Aluminium	Nee
3U260VITA48.2 SS-311	3U	ANSI/VITA 48.2-2020	Secundair	Black Anodized	Aluminium	Nee

Catalogusnummer	Rekhoogte	Voldoet aan	Oriëntatie	Afwerking	Materiaal	Snelle verzending
3UVPX48.2-PS260HTSI-311	3U				Aluminium	Nee
6U260IEEE1101.2PS-700	6U		Primair		Aluminium	Nee
6U260VITA30.1PS-700	6U	ANSI/VITA 30.1-2008	Primair		Aluminium	Nee
6U260VITA46.0PS-700	6U	ANSI/VITA 46.0-2019	Primair		Aluminium	Nee
6U260VITA48.2PS-311	6U	ANSI/VITA 48.2-2020	Primair	Black Anodized	Aluminium	Nee
6U260VITA48.2SS-311	6U	ANSI/VITA 48.2-2020	Secundair	Black Anodized	Aluminium	Nee

AANVULLENDE PRODUCTGEGEVENS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE