


BD Two Pole Distribution Block, 40 A.

Data Solutions



SERTIFISERINGER



FUNKSJONER

I samsvar med RoHS

Halogen Fri

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

SPESIFIKASJONER

Katalognummer	BD-40A
Artikkelnummer	563720



Katalognummer	BD-40A
Maks. Strømvurdering, IEC	40A
Kortsiktig motstår strøm (Icw) 1s.	4.5kA
Toppkortslutningsstrøm (IPK)	22kA
Maks arbeidsspenning, IEC (UI)	500
Linje side antall tilkoblinger	2
Linje side kompakt strandet Wire størrelse	6 - 16 mm ²
Linjeside strandet Wire størrelse - Ferrule	4 – 10mm ²
Antall koblinger på lastsiden	15
Last side kompakt strandet Wire størrelse	(15) 1,5 - 4 mm ²
Sideveis strandet Wire Size - Ferrule	(15) 0,75 – 4 mm ²
Dybde (D)	50mm
Høyde (H)	50mm
Bredde (W)	130mm
Vekt på enhet	0.22kg
Brennbarhetsvurdering	UL® 94V-0
Samsvarer med	IEC® 60947-7-1

YTTERLIGERE PRODUKTDETALJER

Line side and load side number of connections are per pole.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE