


DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



FUNKSJONER

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPESIFIKASJONER

Produkttype: DIN-skinne

Table 1/2

Katalognummer	Materiale	Høyde	Lengde	Overflate	Antall pakker	Dybde
20118-872	Stål	35mm	125mm	Sinkbelagt	4	15mm
20118-873	Stål	35mm	175mm	Sinkbelagt	4	15mm
20118-874	Stål	35mm	275mm	Sinkbelagt	4	15mm
20118-875	Stål	35mm	375mm	Sinkbelagt	4	15mm
20118-876	Stål	35mm	475mm	Sinkbelagt	4	15mm

Katalognummer	Materiale	Høyde	Lengde	Overflate	Antall pakker	Dybde
20118-877	Stål	35mm	575mm	Sinkbelagt	4	15mm
20118-878	Stål	35mm	125mm	Sinkbelagt	4	7.5mm
20118-879	Stål	35mm	175mm	Sinkbelagt	4	7.5mm
20118-880	Stål	35mm	275mm	Sinkbelagt	4	7.5mm
20118-881	Stål	35mm	375mm	Sinkbelagt	4	7.5mm
20118-882	Stål	35mm	475mm	Sinkbelagt	4	7.5mm
20118-883	Stål	35mm	575mm	Sinkbelagt	4	7.5mm
20118-890	Stål	35mm	125mm	Sinkbelagt	10	7.5mm
20118-891	Stål	35mm	175mm	Sinkbelagt	10	7.5mm
20118-892	Stål	35mm	275mm	Sinkbelagt	10	7.5mm
20118-893	Stål	35mm	375mm	Sinkbelagt	10	7.5mm
20118-894	Stål	35mm	475mm	Sinkbelagt	10	7.5mm
20118-895	Stål	35mm	575mm	Sinkbelagt	10	7.5mm
20118-884	Stål	35mm	125mm	Sinkbelagt	10	15mm
20118-885	Stål	35mm	175mm	Sinkbelagt	10	15mm
20118-886	Stål	35mm	275mm	Sinkbelagt	10	15mm
20118-887	Stål	35mm	375mm	Sinkbelagt	10	15mm
20118-888	Stål	35mm	475mm	Sinkbelagt	10	15mm

Katalognummer	Materiale	Høyde	Lengde	Overflate	Antall pakker	Dybde
20118-889	Stål	35mm	575mm	Sinkbelagt	10	15mm

Table 2/2

Katalognummer	Bredde
20118-872	125mm
20118-873	175mm
20118-874	275mm
20118-875	375mm
20118-876	475mm
20118-877	575mm
20118-878	125mm
20118-879	175mm
20118-880	275mm
20118-881	375mm
20118-882	475mm
20118-883	575mm
20118-890	125mm
20118-891	175mm
20118-892	275mm
20118-893	375mm

Katalognummer	Bredde
20118-894	475mm
20118-895	575mm
20118-884	125mm
20118-885	175mm
20118-886	275mm
20118-887	375mm
20118-888	475mm
20118-889	575mm

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE