

Motion detector

Data Solutions



Motion detector: Prepared for mounting on door box, detection method: movement, detection fields of radar are adjustable, wide field 4 m (W) x 2 m (D), narrow field 2 m (W) x 2.5 m (D), supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate.

SERTIFISERINGER



FUNKSJONER

Supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate

Wide field 4 m (W) x 2 m (D)

Arrow field 2 m (W) x 2.5 m (D)

Detection method: movement

Prepared for mounting on door box

Detection fields of radar are adjustable

SPESIFIKASJONER

Table 1/1

Katalognummer	Type	Fungerer med	Antall pakker
60130-067	Bevegelsesdetektor	Radbegrensning	1

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE