

# Secure Dual W-Lock Power Cord

## Data Solutions



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

### FUNKSJONER

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

### SPESIFIKASJONER

Table 1/2

| Katalognummer | Type  | Fungerer med | Lengde | Farge | Høyde | Lengde på inngangskabel |
|---------------|-------|--------------|--------|-------|-------|-------------------------|
| EP1314024X150 | Kabel | RackPower    | 600mm  | Svart | 270mm | 588m                    |
| EP1314048X125 | Kabel | RackPower    | 1200mm | Svart | 270mm | 1.176m                  |
| EP1314072X100 | Kabel | RackPower    | 1800mm | Svart | 270mm | 1.764m                  |
| EP1314B24X150 | Kabel | RackPower    | 600mm  | Blå   | 270mm | 0.588m                  |
| EP1314B48X125 | Kabel | RackPower    | 1200mm | Blå   | 270mm | 1.176m                  |

| Katalognummer | Type  | Fungerer med | Lengde | Farge | Høyde | Lengde på inngangskabel |
|---------------|-------|--------------|--------|-------|-------|-------------------------|
| EP1314B72X100 | Kabel | RackPower    | 1800mm | Blå   | 270mm | 1.764m                  |
| EP1314R24X150 | Kabel | RackPower    | 600mm  | Rød   | 270mm | 0.588m                  |
| EP1314R48X125 | Kabel | RackPower    | 1200mm | Rød   | 270mm | 1.176m                  |
| EP1314R72X100 | Kabel | RackPower    | 1800mm | Rød   | 270mm | 1.764m                  |
| EP1920024X100 | Kabel | RackPower    | 600mm  | Svart | 270mm | 0.588m                  |
| EP1920048X75  | Kabel | RackPower    | 1200mm | Svart | 270mm | 1.176m                  |
| EP1920072X50  | Kabel | RackPower    | 1800mm | Svart | 270mm | 1.764m                  |
| EP1920B24X100 | Kabel | RackPower    | 600mm  | Blå   | 270mm | 0.588m                  |
| EP1920B48X75  | Kabel | RackPower    | 1200mm | Blå   | 270mm | 1.176m                  |
| EP1920B72X50  | Kabel | RackPower    | 1800mm | Blå   | 270mm | 1.764m                  |
| EP1920R24X100 | Kabel | RackPower    | 600mm  | Rød   | 270mm | 0.588m                  |
| EP1920R48X75  | Kabel | RackPower    | 1200mm | Rød   | 270mm | 1.176m                  |
| EP1920R72X50  | Kabel | RackPower    | 1800mm | Rød   | 270mm | 1.764m                  |

Table 2/2

| Katalognummer | Antall pakker | Pluggtype | Uttakbar inngangskabel |
|---------------|---------------|-----------|------------------------|
| EP1314024X150 | 150           | C13/C14   | Nei                    |

| Katalognummer | Antall pakker | Pluggtype | Uttakbar inngangskabel |
|---------------|---------------|-----------|------------------------|
| EP1314048X125 | 125           | C13/C14   | Nei                    |
| EP1314072X100 | 100           | C13/C14   | Nei                    |
| EP1314B24X150 | 150           | C13/C14   | Nei                    |
| EP1314B48X125 | 125           | C13/C14   | Nei                    |
| EP1314B72X100 | 100           | C13/C14   | Nei                    |
| EP1314R24X150 | 150           | C13/C14   | Nei                    |
| EP1314R48X125 | 125           | C13/C14   | Nei                    |
| EP1314R72X100 | 100           | C13/C14   | Nei                    |
| EP1920024X100 | 100           | C19/C20   | Nei                    |
| EP1920048X75  | 75            | C19/C20   | Nei                    |
| EP1920072X50  | 50            | C19/C20   | Nei                    |
| EP1920B24X100 | 100           | C19/C20   | Nei                    |
| EP1920B48X75  | 75            | C19/C20   | Nei                    |
| EP1920B72X50  | 50            | C19/C20   | Nei                    |
| EP1920R24X100 | 100           | C19/C20   | Nei                    |
| EP1920R48X75  | 75            | C19/C20   | Nei                    |
| EP1920R72X50  | 50            | C19/C20   | Nei                    |

## ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk,

feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**