

Hydraulikkpumpe og fotkontroller



SERTIFISERINGER



FUNKSJONER

Directly connects to a single hydraulic tool for operation or can be used as a spare for the Hydraulic nVent ERIFLEX Flexibar and Busbar Work Center

Pump includes hose with quick-release coupler

Foot controller includes two pedals with off, on and safety off positions

SPESIFIKASJONER

Table 1/2

Katalognummer	Artikkelnummer	Spenning	Effekt	Driftstrykk	Oljestrøm	Tankekapasitet
HYDR-PMP-230V	545700	230 V	370W	700bar	0.2l/min	1.900 - 3.8 l

Table 2/2

Katalognummer	Artikkelnummer	Vekt på enhet
HYDR-PMP-230V	545700	40 kg

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk
støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE