

CS480 vinkelkobling



CS480 Angle Coupling mounts between a tube and the enclosure to provide tilt option for the machine operator. Rigid flange coupling with 15-degree angle of inclination for attaching enclosure.

BRANSJESTANDARDER

IEC 60529, IP66

FUNKSJONER

Enclosure is mounted at a 15-degree incline angle

Gasket and mounting hardware are included

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPESIFIKASJONER

Table 1/1						
Katalognummer	Høyde	Bredde	Dybde	Materiale	Avslutt	Hurtiglevering
CCSS48AC15	80mm	70mm	70mm	Rustfritt stål 304	Børstet	Nei

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE