

CS480 vinkelkobling for brakett



CS480 Base Bracket Angle Coupling mounts the enclosure directly to horizontal surfaces, enabling 15-degree enclosure tilt.

BRANSJESTANDARDER

IEC 60529, IP66

FUNKSJONER

Enclosure is mounted at a 15-degree incline angle

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPESIFIKASJONER

Table 1/1						
Katalognummer	Høyde	Bredde	Dybde	Materiale	Avslutt	Hurtiglevering
CCSS48ACBB	85mm	109mm	109mm	Rustfritt stål 304	Børstet	Nei

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE