

Interne sidepaneler for kraftdistribusjon, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

FUNKSJONER

Beskrivelse: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Materiale: 1.5 mm galvanized steel.

Levering: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

SPESIFIKASJONER

Tykkelse: 1.5mm
Avslutt: Galvanisert
Materiale: Stål

Table 1/1

Katalognummer	Høyde	Bredde	Dybde	Panelstørrelse	Innkapslingsmateriale	Produktfamilie
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Mild stål	Frittstående
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Mild stål	Frittstående
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Mild stål	Frittstående
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Mild stål	Frittstående
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Mild stål	Frittstående
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Mild stål	Frittstående
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Mild stål	Frittstående
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Mild stål	Frittstående
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Mild stål	Frittstående
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Mild stål	Frittstående
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Mild stål	Frittstående
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Mild stål	Frittstående
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Mild stål	Frittstående
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Mild stål	Frittstående
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Mild stål	Frittstående
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Mild stål	Frittstående

Katalognummer	Høyde	Bredde	Dybde	Panelstørrelse	Innkapslingsmateriale	Produktfamilie
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Mild stål	Frittstående
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Mild stål	Frittstående

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE