

Vertikalt panelkoblingslys, S1MPCV



Suspend 180-Max Vertical Panel Coupling mounts a vertical tube to the back of an enclosure or screen using Video Electronics Standards Association (VESA) mounting. The coupling has mounting holes drilled for standard VESA 75 and 100 flange sizes. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The vertical panel coupling has a safety stop and maintenance-free bearings.

FUNKSJONER

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPESIFIKASJONER

Materiale: Aluminium
Overflate: Pulverbelagt

Table 1/1

Katalognummer	E-nummer	Høyde	Bredde	Dybde	Farge	Fargekode
S1MPCV	2411892	256mm	140mm	120mm	Kullsvart	RAL 9005
S1MPCVG		185mm	120mm	140mm	Lys grå	RAL 7035

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE