

D16 mekanisk ankerplass for kryogene applikasjoner



The nVent LENTON brand of cryogenic reinforcement splicing systems should be specified whenever cryogenic-grade reinforcing bar is used, or during normal operating or emergency conditions where the temperature falls below -20 °C (-4 °F). By combining the nVent LENTON taper-threaded couplers with state-of-the-art materials, we have developed one of the slimmest couplers on the market, while still maintaining top performance. Typical construction projects include LNG and LPG storage tanks.

FUNKSJONER

Replaces conventional hooked reinforcing bar

Simplifies reinforcing bar placement and lowers placing costs

Head area exceeds 5x bar area (net 4x)

Improved performance and reliability at cryogenic temperatures (-168 °C / -270 °F)

SPESIFIKASJONER

Avslutt: Vanlig

Materiale: Rustfritt stål 431 (en 1,4057)

Table 1/1

Katalognummer	Armeringstørrelse, metrisk	Armeringstr., US	Armeringsjern, Canada	Diameter (Ø)	Lengde (L)	Vekt på enhet
EL12D16CRN	12 mm	#4	10M.	35 mm	19mm	0.13 kg
EL16D16CRN	16 mm	#5	15M.	36 mm	24mm	0.16 kg
EL20D16CRN	20 mm	#6	20M.	45 mm	35mm	0.37 kg
EL25D16CRN	25 mm	#8	25M.	60 mm	40mm	0.77 kg


Katalognummer	Armeringstørrelse, metrisk	Armeringstr., US	Armeringsjern, Canada	Diameter (Ø)	Lengde (L)	Vekt på enhet
EL28D16CRN	28 mm	#9	30M.	65 mm	42mm	0.94 kg
EL32D16CRN	32 mm	#10		75 mm	46mm	1.35 kg

YTTERLIGERE PRODUKTDETALJER

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Thread does not need to be flush with end of nVent LENTON Terminator. Thread may be +/- 2 threads from backside of coupler.

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE