

C12SW Side Weldable Half-Coupler, Round, 36 mm, #11, 35M

KATALOGNUMMER

EL36C12SWSP01



SERTIFISERINGER



FUNKSJONER

Designed for connecting reinforcing bar parallel to structural steel sections or plates

Round coupler allows the positioning of bent or hooked bar prior to welding

Machined from weldable grades of steel

PRODUKTEGENSKAPER

Materiale: Stål

Avslutt: Vanlig

Armeringstørrelse, metrisk: 36 mm

Armeringstr., US: #11

Armeringsjern, Canada: 35M.

Diameter (Ø): 50 mm

Lengde (L): 140mm

Søyledybde (BD): 43mm

Vekt på enhet: 1.76 kg

Designet for å møtes: AASHTO; ABNT NBR 8548:1984; ACI 318 type 1 (125 % spesifisert kapasitet); ACI 318 type 2 (spesifisert strekkfasthet); ACI 349; ACI 359; AS3600


Pakkeantall: 8

YTTERLIGERE PRODUKTDETALJER

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

The design of the weld, the selection of electrode, and other relevant choices depend on the chemical and physical properties of the structural steel to which the couplers are welded. Engineers who design assemblies should adhere to all appropriate regulations.

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE