

19" Fan Unit, 1 U, Remote Control and Monitoring

Power Utilities

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

FUNKSJONER

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPESIFIKASJONER

Table 1/2

Katalognummer	Inngangsspenn ing AC	Luftstrøm	Støynivå	Effekt	Maks. Statisk trykk	Omgivelsestem peratur
10713-554	100 – 240 V	1089 m³/h	59.5 dB(A)	97 W	78 Pa	–10 to 70 °C

Table 2/2

Katalognummer	Levetid, L10 ved 40 C.
10713-554	99558 h

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE