

19" Fan Unit, 1 U, Speed Control and Monitoring

Strømforsyning

Fan Unit for installation into a 1 U space within the Cabinet.



SERTIFISERINGER



FUNKSJONER

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPESIFIKASJONER

Table 1/1

Katalognummer	Input Voltage AC	Input Voltage DC	Sertifiseringer
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Katalognummer	Input Voltage AC	Input Voltage DC	Sertifiseringer
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE