

Varistar CP Seismic Base/Plinth, 103H 800W 600D

Strømforsyning

KATALOGNUMMER

21630-115

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FUNKSJONER

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

PRODUKTATTRIBUTTER

Product Type: Cabinet/Rack Base

Product Family: Varistar CP

Type: Base Plinth

Materiell: Stål

Farge: Black Grey

Fargekode: RAL 7021

Høyde: 103 mm

Bredde: 800 mm

Dybde: 800 mm

Complies With: IEC 61587-1; IEC 61587-2

Static Load: 400 N

Works With: Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE