

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

KATALOGNUMMER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

FUNKSJONER

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUKTEGENSKAPER

Produkttype: Skapdør

Produktfamilie: Varistar CP

Type: Ståldør, perforert

Arbeider med: Varistar CP

Låsetype: Enkelpunktslåsing

Farge: Svart grå

Fargekode: RAL 7021

Rackhøyde: 29 U

Høyde: 1400 mm

Bredde: 800 mm

Beskyttelsesgrad: IP20

Samsvarer med: IEC 61587-1

YTTERLIGERE PRODUKTDETALJER

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE