

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Strømforsyning

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



SERTIFISERINGER



FUNKSJONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Dybde	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-161	3 U	175 mm	1	Backplane	160 mm	Rustfritt stål
24567-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Rustfritt stål
24567-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rustfritt stål
24567-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rustfritt stål
24567-461	6 U	175 mm	1	Backplane	160 mm	Rustfritt stål
24567-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Rustfritt stål
24567-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rustfritt stål
24567-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rustfritt stål

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montering	Samsvarer med	EMC Shielding	Product Type
24567-161	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-162	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-163	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-164	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-461	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-462	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	HandleIncluded	Montering	Samsvarer med	EMC Shielding	Product Type
24567-463	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis
24567-464	5 g (force)	Ja	Rack	IEC 60297-3-103	Nei	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statisk belastning	Sertifiseringer
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE