


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

Strømforsyning

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



SERTIFISERINGER



FUNKSJONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Dybde	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montering	Samsvarer med	EMC Shielding	Product Type
24563-172	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis
24563-173	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis
24563-174	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis
24563-472	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis
24563-473	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis
24563-474	5 g (force)	Nei	Rack	IEC 60297-3-103	Ja	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statisk belastning
24563-172	84 HP	15 kgf
24563-173	84 HP	15 kgf

Katalognummer	Rack Width	Statisk belastning
24563-174	84 HP	15 kgf
24563-472	84 HP	15 kgf
24563-473	84 HP	15 kgf
24563-474	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE