

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



SERTIFISERINGER



FUNKSJONER

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPESIFIKASJONER

Table 1/2

Katalognummer	Rackhøyde	Dybde	Pakkeantall	For montering	Styredybde	Håndtak inkludert
24564-433	6 U	295 mm	1	Bakplan	160 mm, 220 mm, 280 mm	Nei
24564-432	6 U	235 mm	1	Bakplan	160 mm, 220 mm	Nei
24564-431	6 U	175 mm	1	Bakplan	160 mm	Nei
24564-133	3 U	295 mm	1	Bakplan	160 mm, 220 mm, 280 mm	Nei
24564-132	3 U	235 mm	1	Bakplan	160 mm, 220 mm	Nei
24564-131	3 U	175 mm	1	Bakplan	160 mm	Nei

Table 2/2

Katalognummer	Montering	Samsvarer med	EMC-skjerming	Produkttype	Rackbredde	Statisk belastning
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nei	Subrack/chassis	84 HP	7.5 kgf

YTTERLIGERE PRODUKTDETALJER

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell.

Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE