


EuropacPRO 19" Subrack Kit for Backplane, Shielded

Strømforsyning

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



SERTIFISERINGER



FUNKSJONER

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPESIFIKASJONER

Product Type: Subrack/Chassis

Table 1/2

Katalognummer	Rack Height	Dybde	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/2

Katalognummer	Handle Included	Montering	Samsvarer med	EMC Shielding	Rack Width	Statisk belastning
24563-142	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-143	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-144	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-145	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

Katalognummer	HandleIncluded	Montering	Samsvarer med	EMC Shielding	Rack Width	Statisk belastning
24563-146	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-442	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-443	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-444	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-445	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-446	Nei	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE