


EuropacPRO 19" Subrack Kit for Power Distribution Module, Unshielded

Strømforsyning



For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted.

SERTIFISERINGER



FUNKSJONER

For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted

Modular frame to accept e.g. power distribution modules

Internal and external dimensions in accordance with the IEC 60297-3-101 and IEEE 1101.1 standards

Aluminium side panels

Horizontal rails type "light"

IEEE 1101.1 compatible

SPESIFIKASJONER

Table 1/2

Katalognummer	Product Type	Rack Height	Rack Width	Dybde	For Mounting	EMC Shielding
---------------	--------------	-------------	------------	-------	--------------	---------------

24563-100	Subrack/Chassis	3 U	84 HP	115 mm	Power Distribution Module	Nei
-----------	-----------------	-----	-------	--------	---------------------------	-----

Table 2/2

Katalognummer	Statisk belastning	Handle Included	Montering	Samsvarer med	Package Quantity
24563-100	2.5 kgf	Nei	Rack	IEC 60297-3-103	1

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE