

EuropacPRO Cover Plate for Bolting to Rugged Side Panel

Strømforsyning



A cover plate is used for electromagnetic shielding or as mechanical protection.

SERTIFISERINGER



FUNKSJONER

Perforation degree 58%

SPESIFIKASJONER

Table 1/2

Katalognummer	Dybde	Package Quantity	Product Family	Product Type	Rack Width	Type
24568-036	277.75 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert
24568-012	295 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert
24568-008	235 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert

Katalognummer	Dybde	Package Quantity	Product Family	Product Type	Rack Width	Type
24568-032	275 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert
24568-004	175 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert
24568-016	295 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert
24568-020	355 mm	1	EuropacPRO	Dekkplate	84 HP	Perforert

Table 2/2

Katalognummer	Fungerer med	Emballasjeenhet	Dreiemoment
24568-036	Subracks	Par	2.1 N·m
24568-012	Subracks	Par	2.1 N·m
24568-008	Subracks	Par	2.1 N·m
24568-032	Subracks	Par	2.1 N·m
24568-004	Subracks	Par	2.1 N·m
24568-016	Subracks	Par	2.1 N·m
24568-020	Subracks	Par	2.1 N·m

ADDITIONAL PRODUCT DETAILS

A top cover locking mechanism is optionally available that also fixes the top cover in the front and rear guide rail.

4 stainless steel EMC contact strips per subrack are required for shielding, please order separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE