

Front Panel, Anodized With Untreated Edges, Unshielded

Strømforsyning



Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

SERTIFISERINGER



FUNKSJONER

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-271	2 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-331	3 U	63 HP	1	Ingen	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Ingen	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Ingen	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Ingen	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Ingen	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Ingen	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Ingen	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Ingen	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Ingen	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Ingen	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Ingen	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Ingen	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Ingen	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Ingen	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Ingen	Screw-on Front	Anodized
30818-284	3 U	16 HP		Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-289	3 U	21 HP	5	Ingen	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Ingen	Screw-on Front	Anodized
30818-517	6 U	3 HP		Ingen	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Ingen	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Ingen	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Ingen	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Ingen	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Ingen	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Ingen	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Ingen	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Ingen	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Ingen	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Ingen	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Ingen	Screw-on Front	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30818-271	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	84 mm	Aluminium
30818-310	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30818-331	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-352	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-434	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	172.9 mm	Aluminium
30818-556	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-577	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-598	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30810-433	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-747	Anodized	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-272	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-273	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-274	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-275	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-276	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-277	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30818-279	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-281	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-282	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-284	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-289	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-296	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30818-517	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-518	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-519	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-520	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-521	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-522	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-524	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-526	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30818-528	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-530	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-535	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30818-542	Anodized	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30818-271	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-310	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-331	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-352	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-434	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-556	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-577	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-598	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30810-433	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-747	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-272	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30818-273	Front Panel	Front Panel without Handle	20 mm	RoHS

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30818-274	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-275	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-276	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-277	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-279	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-281	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30818-282	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-284	Front Panel	Front Panel without Handle	80.9 mm	
30818-289	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-296	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30818-517	Front Panel	Front Panel without Handle	14.9 mm	
30818-518	Front Panel	Front Panel without Handle	20 mm	RoHS
30818-519	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-520	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-521	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-522	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-524	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-526	Front Panel	Front Panel without Handle	60.6 mm	RoHS

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30818-528	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-530	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30818-535	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-542	Front Panel	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE