

Front Panel, Front Anodized, Rear Conductive, Unshielded

Strømforsyning

Front panel, unshielded, front anodized and rear conductive.



SERTIFISERINGER



FUNKSJONER

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30838-123	3 U	84 HP	1	Ingen	Screw-on Front	Anodized
30838-204	6 U	84 HP	1	Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30847-465	4 U	84 HP	1	Ingen	Screw-on Front	Anodized
30847-469	5 U	84 HP	1	Ingen	Screw-on Front	Anodized
30847-461	2 U	84 HP	1	Ingen	Screw-on Front	Anodized
30838-081	3 U	42 HP	1	Ingen	Screw-on Front	Anodized
30838-102	3 U	63 HP	1	Ingen	Screw-on Front	Anodized
30838-162	6 U	42 HP	1	Ingen	Screw-on Front	Anodized
30838-183	6 U	63 HP	1	Ingen	Screw-on Front	Anodized
30847-459	2 U	42 HP	1	Ingen	Screw-on Front	Anodized
30847-460	2 U	63 HP	1	Ingen	Screw-on Front	Anodized
30847-463	4 U	42 HP	1	Ingen	Screw-on Front	Anodized
30847-464	4 U	63 HP	1	Ingen	Screw-on Front	Anodized
30847-467	5 U	42 HP	1	Ingen	Screw-on Front	Anodized
30847-468	5 U	63 HP	1	Ingen	Screw-on Front	Anodized
30847-458	2 U	28 HP	5	Ingen	Screw-on Front	Anodized
30847-470	3 U	2 HP	5	Ingen	Screw-on Front	Anodized
30838-067	3 U	28 HP	5	Ingen	Screw-on Front	Anodized
30838-043	3 U	4 HP	5	Ingen	Screw-on Front	Anodized
30838-044	3 U	5 HP	5	Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30838-045	3 U	6 HP	5	Ingen	Screw-on Front	Anodized
30838-046	3 U	7 HP	5	Ingen	Screw-on Front	Anodized
30838-047	3 U	8 HP	5	Ingen	Screw-on Front	Anodized
30838-049	3 U	10 HP	5	Ingen	Screw-on Front	Anodized
30838-051	3 U	12 HP	5	Ingen	Screw-on Front	Anodized
30838-053	3 U	14 HP	5	Ingen	Screw-on Front	Anodized
30838-055	3 U	16 HP		Ingen	Screw-on Front	Anodized
30838-060	3 U	21 HP	5	Ingen	Screw-on Front	Anodized
30847-471	3 U	3 HP	5	Ingen	Screw-on Front	Anodized
30847-476	4 U	4 HP	5		Screw-on Front	Anodized
30847-462	4 U	28 HP	5	Ingen	Screw-on Front	Anodized
30838-124	6 U	4 HP	5	Ingen	Screw-on Front	Anodized
30847-466	5 U	28 HP	5	Ingen	Screw-on Front	Anodized
30838-125	6 U	5 HP	5	Ingen	Screw-on Front	Anodized
30838-126	6 U	6 HP	5	Ingen	Screw-on Front	Anodized
30838-127	6 U	7 HP	5	Ingen	Screw-on Front	Anodized
30838-128	6 U	8 HP	5	Ingen	Screw-on Front	Anodized
30838-130	6 U	10 HP	5	Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30838-132	6 U	12 HP	5	Ingen	Screw-on Front	Anodized
30838-134	6 U	14 HP	5	Ingen	Screw-on Front	Anodized
30838-136	6 U	16 HP	5	Ingen	Screw-on Front	Anodized
30838-141	6 U	21 HP	5	Ingen	Screw-on Front	Anodized
30838-148	6 U	28 HP	5	Ingen	Screw-on Front	Anodized
30847-480	9 U	8 HP	5		Screw-on Front	Anodized
30847-482	9 U	10 HP	5		Screw-on Front	Anodized
30847-484	9 U	12 HP	5		Screw-on Front	Anodized
30847-556	9 U	84 HP	5	Ingen	Screw-on Front	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30838-123	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-204	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30847-465	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	172.9 mm	Aluminium
30847-469	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	217.4 mm	Aluminium
30847-461	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	84 mm	Aluminium
30838-081	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30838-102	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-162	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-183	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30847-459	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	84 mm	Aluminium
30847-460	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	84 mm	Aluminium
30847-463	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	172.9 mm	Aluminium
30847-464	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	172.9 mm	Aluminium
30847-467	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	217.4 mm	Aluminium
30847-468	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	217.4 mm	Aluminium
30847-458	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	84 mm	Aluminium
30847-470	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-067	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-043	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-044	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30838-045	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-046	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-047	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-049	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-051	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-053	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-055	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30838-060	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30847-471	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium
30847-476	Conductive	Nei		Nei	395.1 mm	Aluminium
30847-462	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	172.9 mm	Aluminium
30838-124	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30847-466	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	217.4 mm	Aluminium
30838-125	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Samsvarer med	EMC Shielding	Høyde	Materiell
30838-126	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-127	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-128	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-130	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-132	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-134	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-136	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-141	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30838-148	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	261.8 mm	Aluminium
30847-480	Conductive	Nei		Nei	395.1 mm	Aluminium
30847-482	Conductive	Nei		Nei	395.1 mm	Aluminium
30847-484	Conductive	Nei		Nei	395.1 mm	Aluminium
30847-556	Conductive	Nei	IEC 60297-3-101, IEEE 1101.1/10	Nei	395.1 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30838-123	Front Panel	Front Panel without Handle	426.4 mm	RoHS

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30838-204	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30847-465	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30847-469	Front Panel	Front Panel without Handle	426.4 mm	
30847-461	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30838-081	Front Panel	Front Panel without Handle	213 mm	RoHS
30838-102	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30838-162	Front Panel	Front Panel without Handle	213 mm	RoHS
30838-183	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30847-459	Front Panel	Front Panel without Handle	213 mm	
30847-460	Front Panel	Front Panel without Handle	319.7 mm	
30847-463	Front Panel	Front Panel without Handle	213 mm	RoHS
30847-464	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30847-467	Front Panel	Front Panel without Handle	213 mm	
30847-468	Front Panel	Front Panel without Handle	319.7 mm	
30847-458	Front Panel	Front Panel without Handle	141.9 mm	
30847-470	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30838-067	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30838-043	Front Panel	Front Panel without Handle	20 mm	RoHS

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30838-044	Front Panel	Front Panel without Handle	25 mm	RoHS
30838-045	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30838-046	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30838-047	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30838-049	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30838-051	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30838-053	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30838-055	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30838-060	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30847-471	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30847-476	Front Panel	Front Panel without Handle	20 mm	RoHS
30847-462	Front Panel	Front Panel without Handle	141.9 mm	
30838-124	Front Panel	Front Panel without Handle	20 mm	RoHS
30847-466	Front Panel	Front Panel without Handle	141.9 mm	
30838-125	Front Panel	Front Panel without Handle	25 mm	RoHS
30838-126	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30838-127	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30838-128	Front Panel	Front Panel without Handle	40.3 mm	RoHS

Katalognummer	Product Type	Type	Bredde	Sertifiseringer
30838-130	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30838-132	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30838-134	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30838-136	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30838-141	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30838-148	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30847-480	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30847-482	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30847-484	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30847-556	Front Panel	Front Panel without Handle	426.4 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE