


Horizontal Rails Threaded Insert, M2.5

Strømforsyning



The threaded insert is a metal strip with thread M2.5 and allows the fixing of front panels.

SERTIFISERINGER



FUNKSJONER

The collar screws used for fixing partial-width front panels must be 12.3 mm long

Usable for all horizontal rails

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Width	Package Quantity	Lengde	Materiell	Product Family	Product Type
34561-384	84 HP	1	431.3 mm	Stål	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

Katalognummer	Rack Width	Package Quantity	Lengde	Materiell	Product Family	Product Type
34561-328	28 HP	1	146.82 mm	Stål	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-342	42 HP	1	217.94 mm	Stål	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-363	84 HP	1	324.62 mm	Stål	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

Table 2/2

Katalognummer	Fungerer med
34561-384	Subracks, Cases
34561-328	Subracks, Cases
34561-342	Subracks, Cases
34561-363	Subracks, Cases

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE