

# Novastar Cabinet Without Door and Rear Panel

## Strømforsyning



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

## SERTIFISERINGER



## FUNKSJONER

Static load-carrying capacity up to 400 kg (see specification table)

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Colors: RAL 7021 or color combination RAL 7021/ RAL 7035

Bolted, die-cast frame with Al extrusions

Without door and rear panel

## SPESIFIKASJONER

Table 1/3

| Katalognummer | Rack Height | Frame Color | Høyde | Frame Color Code | Cladding Material | Bredde |
|---------------|-------------|-------------|-------|------------------|-------------------|--------|
|---------------|-------------|-------------|-------|------------------|-------------------|--------|

|           |      |            |         |          |      |        |
|-----------|------|------------|---------|----------|------|--------|
| 15230-001 | 9 U  | Black Grey | 456 mm  | RAL 7021 | Stål | 553 mm |
| 16230-001 | 9 U  | Black Grey | 456 mm  | RAL 7021 | Stål | 553 mm |
| 15230-002 | 12 U | Black Grey | 589 mm  | RAL 7021 | Stål | 553 mm |
| 15230-003 | 12 U | Black Grey | 589 mm  | RAL 7021 | Stål | 553 mm |
| 16230-002 | 12 U | Black Grey | 589 mm  | RAL 7021 | Stål | 553 mm |
| 16230-003 | 12 U | Black Grey | 589 mm  | RAL 7021 | Stål | 553 mm |
| 15230-004 | 16 U | Black Grey | 767 mm  | RAL 7021 | Stål | 553 mm |
| 15230-005 | 16 U | Black Grey | 767 mm  | RAL 7021 | Stål | 553 mm |
| 16230-004 | 16 U | Black Grey | 767 mm  | RAL 7021 | Stål | 553 mm |
| 16230-005 | 16 U | Black Grey | 767 mm  | RAL 7021 | Stål | 553 mm |
| 15230-006 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 15230-007 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 15230-008 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 16230-006 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 16230-007 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 16230-008 | 20 U | Black Grey | 945 mm  | RAL 7021 | Stål | 553 mm |
| 15230-009 | 25 U | Black Grey | 1167 mm | RAL 7021 | Stål | 553 mm |
| 15230-010 | 25 U | Black Grey | 1167 mm | RAL 7021 | Stål | 553 mm |
| 16230-009 | 25 U | Black Grey | 1167 mm | RAL 7021 | Stål | 553 mm |

|           |      |            |         |          |      |        |
|-----------|------|------------|---------|----------|------|--------|
| 16230-010 | 25 U | Black Grey | 1167 mm | RAL 7021 | Stål | 553 mm |
| 15230-011 | 34 U | Black Grey | 1567 mm | RAL 7021 | Stål | 553 mm |
| 15230-012 | 34 U | Black Grey | 1567 mm | RAL 7021 | Stål | 553 mm |
| 16230-011 | 34 U | Black Grey | 1567 mm | RAL 7021 | Stål | 553 mm |
| 16230-012 | 34 U | Black Grey | 1567 mm | RAL 7021 | Stål | 553 mm |
| 15230-013 | 38 U | Black Grey | 1745 mm | RAL 7021 | Stål | 553 mm |
| 15230-014 | 38 U | Black Grey | 1745 mm | RAL 7021 | Stål | 553 mm |
| 16230-013 | 38 U | Black Grey | 1745 mm | RAL 7021 | Stål | 553 mm |
| 16230-014 | 38 U | Black Grey | 1745 mm | RAL 7021 | Stål | 553 mm |
| 15230-015 | 43 U | Black Grey | 1967 mm | RAL 7021 | Stål | 553 mm |
| 15230-016 | 43 U | Black Grey | 1967 mm | RAL 7021 | Stål | 553 mm |
| 16230-015 | 43 U | Black Grey | 1967 mm | RAL 7021 | Stål | 553 mm |
| 16230-016 | 43 U | Black Grey | 1967 mm | RAL 7021 | Stål | 553 mm |
| 15230-017 | 47 U | Black Grey | 2145 mm | RAL 7021 | Stål | 553 mm |
| 15230-018 | 47 U | Black Grey | 2145 mm | RAL 7021 | Stål | 553 mm |
| 16230-017 | 47 U | Black Grey | 2145 mm | RAL 7021 | Stål | 553 mm |
| 16230-018 | 47 U | Black Grey | 2145 mm | RAL 7021 | Stål | 553 mm |

Table 2/3

| Katalognummer | Cladding Color | Dybde | Statisk belastning | Cladding Color Code | Samsvarer med | Frame Material |
|---------------|----------------|-------|--------------------|---------------------|---------------|----------------|
|---------------|----------------|-------|--------------------|---------------------|---------------|----------------|

|           |            |        |         |          |                 |           |
|-----------|------------|--------|---------|----------|-----------------|-----------|
| 15230-001 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-001 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-002 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-003 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-002 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-003 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-004 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-005 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-004 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-005 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-006 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-007 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-008 | Black Grey | 800 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-006 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-007 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-008 | Light Grey | 800 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-009 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-010 | Black Grey | 800 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-009 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |

|           |            |        |         |          |                 |           |
|-----------|------------|--------|---------|----------|-----------------|-----------|
| 16230-010 | Light Grey | 800 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-011 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-012 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-011 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-012 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-013 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-014 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-013 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-014 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-015 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-016 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-015 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-016 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 15230-017 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 15230-018 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminium |
| 16230-017 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |
| 16230-018 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminium |

Table 3/3

| Katalognummer | Product Type |
|---------------|--------------|
| 15230-001     | Cabinet      |

| Katalognummer | Product Type |
|---------------|--------------|
| 16230-001     | Cabinet      |
| 15230-002     | Cabinet      |
| 15230-003     | Cabinet      |
| 16230-002     | Cabinet      |
| 16230-003     | Cabinet      |
| 15230-004     | Cabinet      |
| 15230-005     | Cabinet      |
| 16230-004     | Cabinet      |
| 16230-005     | Cabinet      |
| 15230-006     | Cabinet      |
| 15230-007     | Cabinet      |
| 15230-008     | Cabinet      |
| 16230-006     | Cabinet      |
| 16230-007     | Cabinet      |
| 16230-008     | Cabinet      |
| 15230-009     | Cabinet      |
| 15230-010     | Cabinet      |
| 16230-009     | Cabinet      |

| Katalognummer | Product Type |
|---------------|--------------|
| 16230-010     | Cabinet      |
| 15230-011     | Cabinet      |
| 15230-012     | Cabinet      |
| 16230-011     | Cabinet      |
| 16230-012     | Cabinet      |
| 15230-013     | Cabinet      |
| 15230-014     | Cabinet      |
| 16230-013     | Cabinet      |
| 16230-014     | Cabinet      |
| 15230-015     | Cabinet      |
| 15230-016     | Cabinet      |
| 16230-015     | Cabinet      |
| 16230-016     | Cabinet      |
| 15230-017     | Cabinet      |
| 15230-018     | Cabinet      |
| 16230-017     | Cabinet      |
| 16230-018     | Cabinet      |

## ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på [www.nvent.com](http://www.nvent.com) og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk,

feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**