

Outdoor Unibody HEX

Strømforsyning



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

SERTIFISERINGER



FUNKSJONER

Double-walled, Al

Forced heat dissipation via integrated heat exchanger in the door, max. 70 W/K

IP 55

One-piece inner case with removable outer cladding

SPESIFIKASJONER

Table 1/2

Katalognummer	Product Type	Product Family	Rack Height	Høyde	Bredde	Dybde
11249-016	Outdoor Cabinet	Unibody	25 U	1330 mm	700 mm	500 mm

Table 2/2

Katalognummer	Wall Type	Door Type	Access	Kjøling	EMC Shielding	Samsvarer med
11249-016	Double Walled	Single Door	Front	Air-to-Air Heat Exchanger	Nei	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE