

PBC flette i strømshunt

Strømforsyning



SERTIFISERINGER



FUNKSJONER

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

SPESIFIKASJONER

Table 1/2

Katalognummer	Artikkelnummer	ΔT 30 K	ΔT 50 K	A	B	C
PBC100X250	564000	349 A	462 A	35 mm	40 mm	7 mm

Table 2/2


Katalognummer	Artikkelnummer	2 Bar Current Coefficient
---------------	----------------	---------------------------

PBC100X250	564000	1.72
------------	--------	------

ADDITIONAL PRODUCT DETAILS

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

DIAGRAMMER



ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnløtelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE