

RackPower Basic PDU, RB0xxx, 100-240 VAC, 1-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

FUNKSJONER

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPESIFIKASJONER

Table 1/2

Katalognummer	Produkttype	Sokkeltype	Farge	Lengde	Spennings AC	Dybde
RB0322	Socket Strip	IEC C13, IEC C19	Svart	817 mm	230 V	53 mm

Table 2/2

Katalognummer	Bredde
RB0322	52 mm

YTTERLIGERE PRODUKTDETALJER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE