

RackPower PDU, RP2xxx, 230 VAC, 1-phase

Strømforsyning

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

FUNKSJONER

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Connecting cable 3 m, with IEC 60309 332P6 connector

C13, C19 outlets

User-defined power-on time delay or automatic power-on sequencing

SPESIFIKASJONER

Table 1/2

Katalognummer	Product Type	Socket Type	Farge	Lengde	Spenning AC	Funksjon
RP2325	Socket Strip	IEC C13, IEC C19	Sort	1750 mm	230 V	Input Monitored, Switched Outlets

Table 2/2

Katalognummer	Dybde	Bredde
RP2325	53 mm	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE