

RackPower PDU, RP2xxx, 230/400 VAC, 3-phase

Power Utilities

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

FUNKSJONER

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

User-defined power-on time delay or automatic power-on sequencing

SPESIFIKASJONER

Table 1/2

Katalognummer	Produkttype	Sokkeltype	Farge	Lengde	Spennings AC	Funksjon
RP2950	Socket Strip	IEC C13, IEC C13/C19	Svart	1826 mm	230 V	Input overvåket, Bytt uttak
RP2850	Socket Strip	IEC C13, IEC C13/C19	Svart	1780 mm	230 V	Input overvåket, Bytt uttak
RP2450	Socket Strip	IEC C13, IEC C13/C19	Svart	1490 mm	230 V	Input overvåket, Bytt uttak

Table 2/2

Katalognummer	Dybde	Bredde
RP2950	75 mm	56 mm
RP2850	75 mm	56 mm
RP2450	75 mm	56 mm

YTTERLIGERE PRODUKTDETALJER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE