

RackPower PDU, RP6xxx, 230 VAC, 1-phase

Power Utilities

Modular, compact intelligent PDU with inlet and outlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

FUNKSJONER

RackPower RP6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Connecting cable 10", with IEC 60309 332P6 connector

C13, C19 outlets

User-defined power-on time delay or automatic power-on sequencing and monitoring of each individual outlet

SPESIFIKASJONER

Table 1/2

Katalognummer	Produkttype	Sokkeltype	Farge	Lengde	Spennings AC	Funksjon
RP6325	Socket Strip	IEC C13, IEC C19	Svart	1750 mm	230 V	Input overvåket, Uttak overvåket, Bytt uttak

Table 2/2

Katalognummer	Dybde	Bredde
RP6325	53 mm	52 mm

YTTERLIGERE PRODUKTDETALJER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE