


U-profile Front Panel, Shieldable, D-Sub Cutouts

Strømforsyning



U-profile front panel with cutout for D-Sub connectors.
Shieldable for textile EMC gasket.

SERTIFISERINGER



FUNKSJONER

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPESIFIKASJONER

Table 1/3

Katalognummer	Package Quantity	Montering	EMC Gasket Type	Front Finish	Rear Finish	Treated Edges
30849-749	5	Screw-on Front	Textile	Anodized	Conductive	Nei

Katalognummer	Package Quantity	Montering	EMC Gasket Type	Front Finish	Rear Finish	Treated Edges
30849-750	5	Screw-on Front	Textile	Anodized	Conductive	Nei
30849-751	5	Screw-on Front	Textile	Anodized	Conductive	Nei
30849-752	5	Screw-on Front	Textile	Anodized	Conductive	Nei
30849-753	5	Screw-on Front	Textile	Anodized	Conductive	Nei
30849-754	5	Screw-on Front	Textile	Anodized	Conductive	Nei
30849-755	5	Screw-on Front	Textile	Anodized	Conductive	Nei

Table 2/3

Katalognummer	Samsvarer med	EMC Shielding	Høyde	Materiell	Product Type	Rack Height
30849-749	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-750	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-751	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-752	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-753	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-754	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U
30849-755	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium	Front Panel	3 U

Table 3/3

Katalognummer	Rack Width	Type	Bredde
---------------	------------	------	--------

30849-749	4 HP	Front Panel without Handle	20 mm
30849-750	4 HP	Front Panel without Handle	20 mm
30849-751	4 HP	Front Panel without Handle	20 mm
30849-752	4 HP	Front Panel without Handle	20 mm
30849-753	4 HP	Front Panel without Handle	20 mm
30849-754	4 HP	Front Panel without Handle	20 mm
30849-755	4 HP	Front Panel without Handle	20 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil.

Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE